



# EVO-STIK Epoxy Express Syringe

## A TWO PART, MULTIPURPOSE EPOXY RESIN ADHESIVE

Date: 14 September 2015

Fact Sheet No.: TDS01668

### YOUR SMART ADVANTAGES

- Gives a strong, long lasting bond and sets clear in minutes
- Ideal for fixing uneven breaks on most materials
- Syringe enables equal amounts of resin and hardener to be dispensed and features a resealable cap

### USES

EVO-STIK Epoxy Express Syringe is a solvent free, low odour, two-part epoxy adhesive. EVO-STIK Epoxy Express Syringe will bond a wide range of materials including metal, wood, masonry, ceramics, glass, leather, rubber, chipboard, concrete, cardboard, fabric and most plastics.

### PRODUCT CHARACTERISTICS

Colour	Resin: Pale Yellow Hardener: Pale Yellow
Form	Liquid
Specific Gravity	1.14 approx.
Composition	Resin: Epoxy Resin Hardener: Amine Hardener
Product Code	30613671 1 x 6 25ml syringe in blisters
Storage/Shelf Life	Store for up to 12 months when stored in original, unopened packaging under cool, dry conditions within the temperature range of +5°C to +25°C.

### TYPICAL PERFORMANCE DATA (Approx.)

Flammability	Non-flammable
Setting Time	3 to 4 minutes at 23°C
Application Temperature	+5°C to +30°C
Service Temperature	-40°C to +70°C
Sandability	Sandable. Please wear a dust mask.
Paintability	Good, but confirm by test. Fine sanding helps. Please wear a dust mask.

### DIRECTIONS FOR USE

IMPORTANT: Before using EVO-STIK Epoxy Express Syringe refer to the relevant Health & Safety Data Sheet, available at [www.bostik.co.uk](http://www.bostik.co.uk).

### PREPARATION

1. Make sure surfaces are dry, clean and free from dust, dirt and grease. For even better bonding slightly roughen surfaces with a suitable abrasive paper.
2. Following the instructions on the back of the blister card, dispense equal volumes of resin and hardener onto a clean disposable surface or the tray provided. Wearing gloves is recommended. Not mixing according to instructions will weaken the bond. Stir well for 30 seconds with the plastic spatula provided, ensuring a thorough mix. Use immediately. Attach the resealable cap to the nozzle as soon as possible.

### APPLICATION

3. Apply the mixed adhesive to both surfaces of the joint and assemble carefully (a layer of adhesive 0.10 to 0.20mm thick will normally impart the greatest lap shear strength to the joint).



FM 01696  
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 [www.bostik.co.uk](http://www.bostik.co.uk)

Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.

4. Keep the joint supported until set (using clamps or tape etc.). Allow 30 minutes before rough handling/machining. Under normal conditions EVO-STIK Epoxy Express Syringe attains its full strength after 24 hours at 20°C. Exact setting time depends on temperatures and the quantities mixed. Setting times may be shorter in hot weather. In cold conditions the rate of curing of the mixed adhesive may be slowed down significantly and weak joints may result. Best results are achieved at between 20°C to 25°C.
5. For a perfect finish carefully remove any excess adhesive with a sharp knife before the adhesive has fully hardened.

#### CLEANING

6. Uncured resin/hardener mixtures can be cleaned from tools using cellulose thinners, acetone or methylated spirits, which is more readily available. Solvents must always be handled with due care as they may be hazardous or flammable.
7. Please note the solvents may attack some rubbers, plastics, painted surfaces, fabrics etc. Bear this in mind if intending to use solvent to remove excess adhesive, and carry out a preliminary test first.
8. Cured adhesive residues can usually be dissolved from tools by soaking in commercial paint stripper. Refer to the paint stripper manufacturer's instructions for use and safe handling. Assess a small trial area before general work.
9. The adhesive may be removed from the skin using a suitable propriety hand cleaner. Contact with the skin should however be avoided. Do not use solvents in contact with the skin. Always open and use adhesive products over a protected surface, and avoid contact with clothing.

#### PRECAUTIONS IN USE

Do not use EVO-STIK Epoxy Express Syringe to repair or make items that will contain food or drink. Not recommended for bonding polyolefin's (e.g. polythene or polypropylene). Thorough mixing is the key to getting a good cured product. Simply stirring leaves unmixed materials at the edges. Always fold in from the edges then re-stir. Cured adhesive may slightly yellow if exposed to sunlight for long periods, even through windows. Not suitable for bonding oven doors or car mirrors.

For any application not covered please contact Technical Services on +44 (0)1785 272625 or visit [www.bostik.co.uk](http://www.bostik.co.uk) for advice.

Recommendations and suggestions are for guidance only, since conditions of use are completely beyond our control.

For health and safety instruction, first aid measures and spillage and disposal instructions, see separate Health and Safety Data Sheet for EVO-STIK Epoxy Express Syringe, available at [www.bostik.co.uk](http://www.bostik.co.uk).

BOSTIK HOTLINE

Smart help +44 (0) 1785 272625



FM 01696  
BS EN ISO 9001:2008

This disclaimer is issued by Bostik Limited ("the Company") and applies to the use of any products supplied by the Company ("the Products") displayed on this Technical Data Sheet ("TDS"). Please read this disclaimer carefully before using any of the Products. Using this TDS and/or the Product constitutes your acceptance of this disclaimer. Its contents shall prevail over any directions of use and any disclaimer and/or exclusion or limitation of liability of the Company which may appear on the packaging of the Products.

This disclaimer sets out the entire financial liability of the Company (including any liability for the acts or omissions of its employees, agents and sub-contractors) to any user of the Products ("Product User") in respect of any use made or resale by the Product User, of any of the Products in this TDS.

This disclaimer does not affect the Company's liability for death or personal injury arising from the Company's negligence in respect of the Products, nor its liability for fraud, or fraudulent misrepresentation, nor any other liability which cannot be excluded or limited under applicable law.

The Company's total liability however arising and whether caused by tort (including negligence and breach of statutory duty), breach of contract or otherwise, arising in connection with the use made or resale by the Product User of any of the Products in this TDS shall be limited to the price paid for the Product by the Product User.

The Company shall not be liable to the Product User for any pure economic loss, loss of profit, loss of business, depletion of goodwill or otherwise, in each case whether direct, indirect or consequential, or any claims (including in respect of personal injury insofar as not caused by the Company's negligence) for consequential compensation whatsoever (howsoever caused) which arise out of or in connection with the use made or resale by the Product User of any of the Products in this TDS.

The Company shall not be liable to the Product User in relation to any loss for any use which is inappropriate or use which is otherwise than in accordance with the relevant instructions for use of the Products in this TDS or on the Product. Product Users are advised to confirm the suitability of the Products by their own tests.

This TDS covers just one of a large range of products supplied by the Company.

Full information on these products and advice on application is freely available from our fully trained staff throughout the country. In addition, specialist technical advice is available from our Technical Services Department. This TDS supersedes all previous TDSs relating to the Products, and users of it must ensure that it is the current issue. Destroy all previous TDS, and if in any doubt, contact the Company, quoting the code number in the top right hand corner on the front of this document.

Sales	Tel: 0844 371 1192	Fax: 01785 241818	<a href="mailto:customer.service@bostik.com">customer.service@bostik.com</a>
Technical Advice	Tel: 0844 371 1197	Fax: 01785 272867	<a href="mailto:technical.service@bostik.com">technical.service@bostik.com</a>
Technical Data & COSHH (MSDS) Data Sheets	Tel: 01785 272625	Fax: 01785 212962	<a href="mailto:stafford.gatehouse@bostik.com">stafford.gatehouse@bostik.com</a>



FM 01696  
BS EN ISO 9001:2008

Bostik Limited, Common Road, Stafford, ST16 3EH, UK. Tel: +44 (0) 1785 272625 [www.bostik.co.uk](http://www.bostik.co.uk)  
Bostik, Evo-Stik & Sealocrete are registered trademarks of Bostik Ltd.